

Product Name :
TIG welding Machines

Product Code :
NLAB-MECHANICALAB260035



Description :

TIG welding Machines

Technical Specification :

TIG Welding Machine offered is made available under model GTA-300 with input voltage of 3 Phase 415+ 10%, frequency of 50/60 Hz, rated input power capacity of 10 KVA and no-load voltage V of 80. These welding machines also feature output current adjustment range (A) of 0-300 with rated output voltage (V) of 22, rated duty cycle 35% of 300 A and rated duty cycle 60% of 250 A. Further, these welding machines also feature rated duty cycle 100% of 210 A, efficiency (%) of 85, power factor (COS ϕ) of 0.93, and insulation class of H. These TIG welding machines also feature protection class of IP21, IP23, suitable welding thickness mm of 0.5 mm to 6mm and quality conformance of STQC, CE, ISO, EN.

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003

