

Product Name :
3 Phase Resistive Load (15A)

Product Code :
NLAB-ELECTRICALAB130007



Description :

3 Phase Resistive Load (15A)

Technical Specification :

5 Control switches given board for current control for Each Phase

Each switch controls 1A current.

15Nos of Rheostats are mounted inside the cabinet having value of 1A.

Rating of Rheostats are 440Ohm,1A at 415V

Current Meter is provided for Load Measurement

Operating Voltage 415V, 50Hz AC (3Phase)

SALIENT FEATURES:

Front panel built with high class insulated Bakelite sheet with Sticker well printed circuits and symbols.

Instruction manual.

3 Phase Indications with 25mm Multi Colored Indicators.

Patch Cords 4mm (Heavy Duty)

High Voltage Test Points are Provided With 4mm Safety Sockets

The trainer is housed in Metal cabinet.

Short Circuit protection with 4Pole MCB.

Size of the trainer set 18"x24"

Easy to move as wheels are given

FAN INSTALLED FOR COOLING

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003