

Product Name :
All Geared Heavy Duty Lathe Machines

Product Code :
NLAB-MACHINELABWK11002



Description :

All Geared Heavy Duty Lathe Machines

Technical Specification :

All Geared Heavy Duty Lathe Machines
1886 .

Spindle Centre

Between Centre

1886

7'

~~3050MM~~ 9'

~~3050MM~~ 10'

~~3050MM~~ 12'

~~3050MM~~ 7'

~~3050MM~~ 9'

~~3050MM~~ 16"

~~3050MM~~ 16"

~~3050MM~~ 4'

~~1500MM~~

~~960MM~~

~~960MM/2'~~

~~960MM/2'~~

~~960MM/4'~~

~~960MM/6'~~

~~960MM/8'~~

~~960MM/20'~~

Centre height 267 mm / 300mm

Main Spindle

Type of spindle nose : A2-6

Spindle nose taper : MT-6

Spindle adaptor morse : MT-4

Taper spindle speeds :12 [30, 43, 55, 85, 115, 160, 210, 285, 400,
545, 785, 1060RPM]} Centre height
267mm

Taper spindle speeds : 12 [20, 28, 38, 55, 75, 105, 140,}
190,265,365,525,705RMP} Centre height
300mm

Spindle mounting on : Taper roller bearings

Tail Stock Spindle

Diameter : 63mm/Travel:180mm/Morse Taper:MT-4

Landing Screw Dia/threads : 38mm/4TPI

Threads

Nos. of threads Range

For fully metric : 17/0.5mm to 15mm/pitch

Norton gear box inch : 40/2 to 60TPI

Feeds

Nos of feeds /range

For fully longitudinal : 40/0,066 to 2mm/rev ,of spindle

Norton gear box cross : 40/0,0165 to 5mm/rev ,of spindle

Center heighte 400mm

Main Spindle

Type Of Spindle nose : Threated TPI

Spindle nose taper : MT-5

Spindle adaptor morse : MT-5

Spindle speeds : 9 nos

RPM/Range : 30-720 RPM

Spindle mounting on : Taper rotter bearings 32224 and 32222 ZKL Make

Tail Stock Spindle

Diameter : 80mm dia

Lending screw dia threade : 500mm TPI

Threads

Nos of threads Range of fully matric : 1 to 14 mm

Nortor Gear box inch : 1 to 30 TPI

Feeds

Nos of feeds

Range for fully longitudinal : 30 nos

Range of longitudinal feed : 0.05 -28mm

Range of Transverse Feed : 0.025-1_4mm

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003