

<b>Product Name :</b> Amplitude Modulation and Demodulation Trainer	<b>Product Code :</b> NLAB-EDUSCHOOLEQ198003
<b>Description :</b>	
Amplitude Modulation and Demodulation Trainer	
<b>Technical Specification :</b>	
SCOPE OF LEARNING:	
Amplitude Modulation	
Amplitude Demodulation	
TECHNICAL SPECIFICATIONS:	
Generator:	
On Board Carrier Generator 100KHz	
On Board Modulating Signal Oscillator 0-1KHz	
Power Supply:	
Fixed DC Power Supplies +15V DC, 250mA	
Operated on Mains power 230V, 50Hz +10%	
Components are mounted on the panels are:	
IC	
Capacitors	
Resistors	
Diode	
SALIENT FEATURES:	

Front panel built with high class insulated Printed Circuit Board sheet with well printed circuits and symbols.

Instruction manual.

Connections are brought out through 4mm Sockets.

Patch Cords 4mm.

The trainer is housed in ABS Plastic cabinet.

Size of the trainer set 12"x8"

## Naugralabequipments

**Website:** www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

**Address:** 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003