

Product Name :
Ampoule Filling and Sealing Machine

Product Code :
NLAB-SCIENTIFICEQ28002



Description :

Ampoule Filling and Sealing Machine (Electric Operated)

Technical Specification :

Machine is built on Slant Travel of Ampoules while filling & sealing, to take care of wide variation of ampoule neck dimensions, thickness of available ampoules as per standard.

The unit is built on S.S. Square pipe frame & totally encompassed with S.S. Coverings, in pleasing mat finish with all aesthetic consideration.

A large opening provided at bottom side for the ease of absolute cleaning

The pendant type electrical control panel is lifted from the machine for ease of operation & safety

Technical Specifications:

No. Of Syringes: 1,2,4,6

Out Put Range/Minute: 10,10 to 30,40 to 100,60 to 120

Ampoule Size Range: 1 to 10 ml.

Pwer Required: 1 HP,1.5 HP

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg,Ambala Cantt,Haryana,India. **Phone:** +91-9896600003