

Product Name :
Closed Cup Flash Point Tester

Product Code :
NLAB-EDUCATIONTVET11003



Description :

Closed Cup Flash Point Tester According To Pensky-Martens (ASTM D93)

Technical Specification :

Measures the flash point: the lowest temperature at which the application of an ignition source ignites the vapors of a sample.

Suitable for the flammability applications of diesel, fuel oil, kerosene and other potentially flammable liquids.

Temperature range: +15 to +370 ° C

Digital temperature display

Ignition source: electric or gas

Propane / butane gas connection

Dimensions: 30 x 46 x 52 cm

Weight: 17 kg

Power supply: 220V - 50Hz

Accessories :

Note: Gas supply to be provided by the customer.

Pressure reducer, 30 mbar

Gas tube, 5 m

Pair of heat resistant gloves, for temperatures up to 260 ° C, size L

Spare parts :

Electric igniter

Agitation coupler

Product temperature sensor

Verification standards:

ASTM D 93 reference liquid, diesel, Pensky-Martens flash point 64.8 ° C, validity 12/2019, 250 ml

ASTM D 93 reference liquid, lubricant, Pensky-Martens flash point 243 ° C, validity 12/2019, 250 ml

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003