

Product Name :

Conversion of Galvanometer Into An Ammeter

Product Code :

NLAB-ELECTRONICSAB420019

Description :

Conversion of Galvanometer Into An Ammeter

Technical Specification :

Conversion of Galvanometer Into An Ammeter

Training Board has been designed specifically for the study of Conversion of a Galvanometer into an Ammeter. The board is absolutely self

contained and requires no other apparatus.

Practical experience on this board carries great educative value for Science and Engineering Students.

Object:

01. To determine the resistance of a Galvanometer by half deflection method.
02. To determine the figure of merit of the Galvanometer.
03. To convert the Galvanometer into an Ammeter of a given range and to calibrate it.

Features:

The board consists of the following built-in parts :

01. +5V D.C. at 50mA, IC regulated Power Supply.
02. Galvanometer, 65mm rectangular dial to read 30-0-30.

03. D.C. Milliammeter, 65mm rectangular dial to read 0-50mA.

04. Potentiometer and adequate no. of other electronic components.

05. Mains ON/OFF switch, Fuse and Jewel light.

The unit is operative on 230V $\pm 10\%$ at 50Hz A.C. Mains.

Adequate no. of patch cords stackable from rear both ends 4mm spring loaded plug length $\frac{1}{2}$ meter.

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003