

Product Name :
Current sensors

Product Code :
EC185



Description :

Current sensors

Technical Specification :

Current sensors Current Sensor, Current Conductor IC , 10 mA, 120 kHz, PFF, 5 Pins, 3 V, 5.5 V
IC, CURRENT SENSOR, 50A, 3CB
Quiescent Current:10mA
Bandwidth:120kHz
Sensor Case Style: PFF
No. of Pins:5Pins
Supply Voltage Min:3V
Supply Voltage Max:5.5V
Operating Temperature Min:-40°C
Operating Temperature Max:150°C
Product Range:ACS758 Famil
Current Sensor, CSLW Series, Open Loop-200mA to 200mA, Sink
Source Output, 4.5 Vdc to 10.5 Vdc
CURRENT SENSOR, +/-0.2A, 4.5V-10.5V
Sensor Output: Sink / Source
Supply Voltage DC Min:4.5V
Supply Voltage DC Max:10.5VDC
Current Measuring Range DC:-200mA to 200mA
Current Measuring Range AC:-200mA to 200mA
Response Time:3µs; Accuracy %:-; Product Current Sensor ic, Overcurrent Fault, 4 mA, 100 kHz, SOIC, 8 Pins,

3 V, 5.5 V CURRENT SENSOR, 12.5A, 3.3V, 8SOIC
Quiescent Current:4mA; Bandwidth:100kHz; Sensor Case
Style: SOIC; No. of Pins:8Pins
Supply Voltage Min:3V
Supply Voltage Max:5.5V
Operating Temperature Min:-40°C
Operating Temperature Max:125°C
Product Range:-; RoH

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg,Ambala Cantt,Haryana,India. **Phone:** +91-9896600003