


Product Name :
Cylindrical Grinder

Product Code :
NLAB-MACHINELABWK22009



Description :

Cylindrical Grinder

Technical Specification :

The Universal Cylindrical Grinding Machine ideally suited to performing repetitive grinding operations or small quantity reduction with equal ease. .

Features of our existing range of machines. All models have hydraulic and mechanical able traverse. Wheel Head rapid approach for the operating conveniently. In all models variable speed of work head and internal grinding spindles facilities are available if required on all models. We use antifriction turcite "B" slid-way material on the slides in all our models. Hand - operated lubrications pump for sufficient lubrication of slides. Surface finish 2 microns (improved values can be obtained by using selected grades of grinding wheel applicable to material to be ground).

Standard attachments :

A coolant pump fitted on a tank, Diamond Dresser 2 nos., Oil can, Dead Center 2 nos., Tool kit.

Additional attachment extra cost :

Internal Grinding Attachment, Balancing Stand, Balancing Mandrel, Three Points Steady Rest, Two points Steady Rest, Radius Truing Device, Spare wheel Flange, Independent Four Jaws Chuck, Magnetic Coolant Pump, Grinding Gauge.

~~3000~~ 3000s

~~Table~~ Table Swivel

~~230mm~~ 230mm Height

WORK HEAD

~~Work Head~~ Work Head Speeds r.p.m. 3 Steps (SGI 305/455/600/800 mm)

~~Morse~~ Morse Taper Center

~~Work Head~~ Work Head Speeds r.p.m. 4 steps (SGI 1000-1250/1500-2000 mm)

~~Morse~~ Morse Taper Center

~~Work Head~~ Work Head Swivel

TABLE

~~Table~~ Table Speeds r.p.m. 4 steps (Mechanical)

~~Table~~ Table Speeds r.p.m. step-less (Hydraulic)

WHEEL HEAD

~~Rapid~~ Rapid approach to all machines

~~Wheel~~ Wheel head with a hand wheel (305/455/600/800)

~~Wheel~~ Wheel head with a hand wheel (1000/1250)

~~Wheel~~ Wheel head with a hand wheel (1500/2000)

~~0.005~~ 0.005mm increments of feed dial

~~Swivel~~ Swivel of wheel head

~~Wheel~~ Wheel speeds (SGI 305/455/600/800 mm)

~~Stand~~ Stand size of wheel 355x

~~38 x 127~~ 38 x 127 mm

~~Wheel~~ Wheel speeds (SGI 1000/1250 mm)

~~Stand~~ Stand size of wheel

~~Wheel~~ Wheel speeds (SGI 1500/2000 mm)

~~Stand~~ Stand size of wheel

POWER

~~Wheel Head~~ Wheel Head (SGI 305/455/600/800/1000/1250 mm)

~~Wheel Head~~ Wheel Head (SGI 1500/2000 mm)

~~M.H. Head~~ M.H. Head (SGI 305/455/600/800 mm)

~~M.H. Head~~ M.H. Head (SGI 1000/1250 mm)

~~W.H. Head~~ W.H. Head (SGI 1500/2000 mm)

~~Mechanical~~ Mechanical Table (SGI 305/455/600/800/1000/1250)

~~Mechanical~~ Mechanical Table (SGI 1500/2000)

Hydraulic
Coolant Pump
Internal Grinding Attachment

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003