

Product Name :
De-Soldering Station

Product Code :
NLAB-ELECTRONICSAB370002



Description :

De-Soldering Station

Technical Specification :

Input Voltage: 190 V to 270V

Output Voltage: 24VAC

Wattage: 70 Watts

Temp range: 180 – 480°C

Temp Accuracy: ± 1 °C

Tip to ground potential: Under 2M.V

Tip to ground Leakage: Under 2

Vacuum: 600 mm/Hg.

High Quality 24V DC Pump with 4000 RPM

Accessories:

Control Unit – 1 No.

Soldering Iron – 1 No.

De-Soldering Iron – 1 No.

Combined Soldering & De-Soldering Stand -1 No.

Power Cord – 1 No.

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003