

Product Name :
Desiccator Vacuum

Product Code :
NLAB-EDUSCHOOLEQ129002



Description :

Desiccator Vacuum

Technical Specification :

Polylab desiccators are made of polypropylene and polycarbonate.

These autoclable vaccum desiccators can hold vaccum upto 740 mm of Hg for 24 hrs without any greasing.

The top dome, moulded in rigid and transparent polycarbonate, gives a crystal clear view of the desiccant placed inside.

The knurled knob on the top provides easy handling of the dome.

The lower part is made of polypropylene.

An internal groove is provided on the flange to hold a silicon rubber O-Ring.

The polypropylene stopcock is fitted with a self lubricating PTFE plug.

This plug works three way i.e. vaccum creation, shutting off & vacucum releasing.

500
300
200
150
100
50
0
D (mm)

150c

200c

250c

300c

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003