

Product Name :
Dial Gauges

Product Code :
TN165



Description :

Dial Gauges

Technical Specification :

This set of mechanical dial gauges enables mechanical travel to be measured. Deflection or displacement can be measured using the dial gauges, as can distances.
The dial gauges can be used for just about every experiment on the Dial Gauge mounting frame. With the aid of rapid action fasteners, the dial gauges can be fitted quickly and securely. The clamps also allow a large range of adjustment.

The unit is perform the following experiments and investigations:

Specifications

Measuring of travel, deformation and displacement in mechanical experiments

2 mechanical dial gauges

Mounted by rapid action fasteners

Technical Data

2 dial gauges

Measuring range: 0...25mm

Measuring range: 0...50mm

Graduation: 0,01mm

Adjustment range of the clamps

0..100mm

0...500mm

Weight: 3kg

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003