

Product Name :
Digital Rework Station 4 in One

Product Code :
NLAB-ELECTRONICSAB370003



Description :

Digital Rework Station 4 in One

Technical Specification :

Input Voltage : 190 V to 270V

Output Voltage : 24VAC

Soldering Wattage : 60 Watts

De-Soldering Wattage : 70 Watts

Temp range : 180-480°C

Temp Accuracy : $\pm 1^\circ\text{C}$

Tip to ground potential : Under 2MV

Tip to ground Leakage : Under 2

Vacuum : 600mm/Hg

High Quality 24 DC Pump with 4000RPM

SMTTweezer : 2 x 25 watts

Motor will switch off automatically after reaching 100°C when the element is switched off

Accessories :

Control Unit 1 No.

Soldering Iron 1 No.

De-Soldering Iron 1 No.

Combined Soldering & De-Soldering Stand 1 No.

SMD Hot Air Iron 1 No.

SMT Hot Tweezer Handle 1 No.

SMD Hot Air Stand 1 No.

Hot Tweezer Stand 1 No.

Power Cord 1 No

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003