

Product Name :
Diode Valve Characteristics Trainer Analog Meters

Product Code :
NLAB-ELECTRICALLAB210050



Description :

Diode Valve Characteristics Trainer Analog Meters

Technical Specification :

SCOPE OF LEARNING:

To draw the Characteristics of Diode

TECHNICAL SPECIFICATIONS:

Power Supplies:

DC Supply 0-30V DC, 150mA

AC Supply 6.3V DC, 2A (Filament)

Operated on Mains power 230V, 50Hz +10%

Analog Meters:

Ammeter 20mA DC.

Voltmeter 30V DC.

Components are mounted on the panels are:

Diode Valve OR COMPATIBLE

Voltage Control through Potentiometer.

Heater (Filament Voltage) Controlled by Toggle Switch.

Series Resistor 470E

SALIENT FEATURES:

Front panel built with high class insulated Printed Circuit Board sheet with well printed circuits and symbols.

Instruction manual.

Connections are brought out through 4mm Colored Sockets.

Patch Cords 4mm.

The trainer is housed in Metal cabinet.

Size of the trainer set 12"x8"

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003