

Product Name :
Direct Shear Apparatus

Product Code :
NLAB-VOCATIONALTVET18024



Description :

Direct Shear Apparatus

Technical Specification :

Display of both speed and displacement with 0.00001 mm resolution

Shear speed between 0.00001 to 9.99999 mm/minute

Max shear effort: 5000 N possible on the whole speed range

Possibility of direct vertical load, or with a lever arm ratio 10:1

Max vertical direct load: 500N; with lever arm: 5500N

Display and pilot lamps to signal any bad functioning and alarms

Box group mounted on ball track with high-quality antifriction system

Read value results are immediate and of extreme accuracy

Extremely easy and practical use, not requiring qualified staff.

Shear box, hollow punch, and tamper are not included in the standard supply and have to be ordered separately
Power supply: 230 V A.C. Single Phase 50Hz

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003