

Product Name :
Glass Distillation Training Unit

Product Code :
NLAB-ENGINEERINGLB54032



Description :

Glass Distillation Training Unit

Technical Specification :

- Working Glass Distillation Training Unit, this actual working glass distillation unit is our full size model.
- The Working Glass Distillation Training Unit is state of the art in teaching process distillation, incorporating a stripper column as well as the main column and includes a custom chilled water unit.
- The pressure system, temperature readouts and controls, pump switch panel and flow controls are centrally located for ease of operation and safety.

We are well-known manufacturers, OEM suppliers of Glass Distillation Training Unit for Applied Machines. Contact us for high quality Glass Distillation Training Unit for Applied Machines for schools lab, college lab, universities, research labs, various teaching and workshop training laboratories and industries in India.

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003