

Product Name :
Hydraulic Press Brakes

Product Code :
NLAB-MACHINELABWK16006



Description :

Hydraulic Press Brakes

Technical Specification :

Hydraulic Press Brakes .

Robust steel frame from ultrasonically tested IS 2062 plates and rigid as per guideline of standards.

Hydraulic cylinder with twin type sealing low & high pressure and hard chrome plated rod with special type guide for long life without leakage.

Repetitive accuracy is within ± 0.04 mm

International quality Hydraulics component rated for 310 bar (Working Pressure is less than 160 bar) which ensure trouble-free operation.

Adjustable five piece guides, provided with special nonmetallic liners for long life.

Quickly adjustable stroke length.

Front operated back gauge with micro setting arrangement.

Ram tilting arrangement to maintain bending accuracy over a period.

Moving work station with ON/OFF buttons, Selector switches for inch, Single cycle & Auto cycle and Emergency Stop buttons for easy

operation and better safety.

Rear Cylinder design using mechanical advantage through lever, reduces the cylinder size which enable to use medium pressure hydraulic component and also improves stroke accuracy.

Fast Approach and fast Return speed for reducing cycle time, Slow pressing speed for better stroke control and bend accuracy

Table length

mm

Bending Capacity

(approx.) mm


~~2800~~ 2800

~~3800~~ 3800

~~4800~~ 4800

~~5800~~ 5800

~~6800~~ 6800



Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003