



IC LM741

Variable Resistor For Gain Setting

**SALIENT FEATURES:**

Front panel built with high class insulated Printed Circuit Board sheet with well printed circuits and symbols.

Instruction manual.

Connections are brought out through 2mm Colored Sockets.

Patch Cords 2mm.

The trainer is housed in ABS Plastic cabinet.

Size of the trainer set 12"x8"

## **Naugralabequipments**

**Website:** [www.naugralabequipments.com](http://www.naugralabequipments.com), **Email:** [sales@naugralabequipments.com](mailto:sales@naugralabequipments.com)

**Address:** 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003