

Product Name :
Laser Diode Intensity Modulation

Product Code :
NLAB-ELECTRONICSAB240012

Description :

Laser Diode Intensity Modulation

Technical Specification :

Laser Diode Intensity Modulation and Demodulation Trainer has been developed to conduct studies on laser Diode, optical fibres and optical communication methods, by signal transmission. Practical experience on this Trainer carries great educative value for Science & Engineering Students.

Experiments:

Characterization of a Laser Diode.

Optical Power (P_o) of a Laser Diode Vs Laser Diode Forward current (I). F

Monitor Photodiode Current (I) Vs Laser Optical Power Output (P_o). M

Study of Automatic Current Control (ACC) or Automatic Power Control (APC) Modes of Operation

Comparison of ACC and APC Modes of Operation.

Design and Evaluation of an Laser Diode (LD) Analog I System M

V_o Vs V_{in} at Specified Optical Carrier Power Levels, P_o .

Determination of V_{in} (max) at Specified P_o for Distortion-free V_o .

Design and Evaluation of Laser Diode LD Digital Transmission System

Risetime and Falltime Pulswidth Distortions and Determination of Propagation Delay.

Transmission of Laser Through an Optical Fibre

To measure loss in dB of Step-index Multimode plastic Fibre Patchcord.

To measure loss in dB of Graded-Index, Multimode Glass Fibre Patchcord.

To measure loss in dB of Two Patchcords connected by the in-line adaptor.

Laser Free Space Communication

Analogue Free Space Communication System.

Digital Free Space Communication System.

Determination of Numerical Aperature of PMMA Fibre Cable

Features:

The trainer consists of the following built-in parts:

Laser Diode Transmitter unit having following built-in parts :

Laser Diode transmitter module.

6V DC at 100mA, IC Regulated Power Supply internally connected.

SPDT switch to select Automatic Current Control (ACC) or Automatic Power Control (APC).

Potentiometer to set power output.

Adequate no of other electronic components.

Mains ON/OFF switch, Fuse and Jewel light.

Laser Diode Receiver unit having following built-in parts :

Laser Diode Receiver Module.

PIN Diode for measuring power of Laser Diode.

Potentiometer to set voltage output.

Adequate no. of other electronic components.

6V DC at 100mA, IC Regulated Power Supply internally connected.

Two-metres PMMA Plastic Fibre patchcord (Cable-1).

Two-metres GI/mm Glass Fibre patchcord (Cable-2).

In-line SMA adaptor.

Numerical Aperature measurement Jig.

Mandrel.

The units are operative on 230V +10% at 50Hz A.C. Mains.

Adequate no. of patch cords stackable 4mm spring loaded plug length 1/2 metre.

Weight : 4 Kg. (Approx)

Dimension : W 340 x H 110 x D 210

Other Apparatus Required:

AF/RF Generator 10Hz to 1 MHz

Three Digital Multimeter

Cathode Ray Oscilloscope 20MHz

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003