

Product Name :
Manual Metal Arc Welding Machine

Product Code :
NLAB-VOCATIONALTVET20016



Description :

Manual Metal Arc Welding Machine

Technical Specification :

Rated voltage: 230V

Input capacity: 3.4kW

Current arrange: 20 to 120A

Rated duty cycle: 60%

Fuse: 20A

Frequency: 50/60Hz

No-load voltage: 68V

Case protection degree: IP21

Arc-starting: 0.93 cos

Efficiency: 80%

Class of insulation: H

Applied welding rod: 1.6 to 3.2 mm

Weight: 5.5 kg

External size: 36 x 23.5 x 30.5 cm

These machines are used for welding following ferrous metals:-

Low carbon steel

Medium carbon steel

Alloy steel

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003