

**Product Name :**  
Mig Welding Machine and Accessories

**Product Code :**  
NLAB-MACHINELABWK34004



**Description :**

Mig Welding Machine and Accessories

**Technical Specification :**

Mobile type MIG/ Pulse MIG Welder

Rated Output: 300A/32V (60% Duty Cycle)

Current Range: 25A to 400A

Applicable Wire Diameter: Steel – Dia. 0.6 to 1.2mm

Aluminum – Dia. 0.9 to 1.2mm

Flux core – Dia. 0.8 to 1.2mm

Wire Feeding speed of Torch: 1.3 to 18m/min

Indication: Digital preferable

Gas solenoid: Must be Equipped

Caster and single cylinder rack: Must be equipped

Features: Automatic arc shut-off, Spot Timer

Wire feeder (type): DC Power type

Cable length: 7.6m

Power Source: 220V 50Hz, single phase

400V 50Hz, three phase

Accessories:

Standard Accessories for MIG Welding – 3 sets

MIG Gun torch with 4.5m cable/contact tips – 3 sets

Ground cable with clamp – 3 sets

Power cord – 2 pcs

Gas regulator/flow-meter – 3 set

Wire feeder – 3 set

Wire drive roll for welding aluminum – reversible U-gooved type – 12 pcs

Gas supply set (including gas cylinder etc., - 3 set)

Spare MIG Gun torch with 4.5m cable /contact tips – 12 set

Operation manual

Spares and consumables must include the following:

Welding Mig guns

Al Welding rods

anti-Spater spray

Welding Wire (Copper Coated)

Standard Welding Equipment Laboratory Set Mig Welding Machine and Accessories  
Manufacturer,Supplier and Mig Welding Machine and Accessories Exporter  
in India

## Naugralabequipments

**Website:** www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

**Address:** 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003