

Product Name :
Mobile Phone Trainer (GSM)

Product Code :
NLAB-ELECTRONICSAB160002



Description :

Mobile Phone Trainer (GSM)

Technical Specification :

Mobile Phone Trainer (GSM) For Electrical Lab Training.

Mobile Phone Trainer (GSM)

Cellular System : EGSM/GSM 900

Rx Frequency band : EGSM 925..960MHz GSM 900 935 .960MHz

Tx Frequency band : EGSM 880 ..8790MHz GSM 90 890 915a MHz

Output power : +5 +33dBm/3.2 mW .0.2W

Channel Spacing : 200KHz

Antenna : Loop type, 50W

Display : 84x48 pixels

On board sections : Antenna, Keypad, SIM, Charging Circuit Clock, User Interface such as Buzzer, Vibrator, LEDs.

Features : Screen saver, Ring tones, SMS etc.

Accessories included : Battery, Mains cord, Manual, Hands Free Kit CD containing Mobile Phone working

Power requirement : 220V $\pm 10\%$ 50Hz

Power consumption : 3.6 Watts (Approx.)

Fuse : 1.5 amps

Housed in Attractive cabinet with Protective cover

Software

: Software CD containing mobile phone working, internal block wise

description call route during outgoing & incoming calls.

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003