

Product Name :
Motorised Pipe Bender

Product Code :
NLAB-MACHINELABWK25002



Description :

Motorised Pipe Bender

Technical Specification :

motorised Hydraulic Pipe Bending Machine ideally suitable for bending water (G.I. Pipes), gas or steam pipes without filling or heating etc., with hydraulic pressure and reverse pressure control, hydraulic motorised pump is suitable for operation on AC 440/3/50 electric supply continuously rated with push button starter gives uniform hydraulic output and faster cylinder operation.

The machine is equipped with "EJECT-O-Mactic" device (except Model AMI-6 & AMI-8 which is segmental type) which takes out pipe from the bending former hydraulically. Complete with standard centre former for G.I. Pipes ("C" class), outer formers and head plates etc. Suitable electricals with 3 phase 440 volts with starter, hydraulic trolley

MOTOR CENTRE

3/2"-3"

3/2" - 4"

3"-4"

Ø" - 6"

Ø" - 8"

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003