

Product Name :
Naugra Polishing Mach Machine

Product Code :
NLAB-ENGINEERINGLB84003



Description :

Naugra Polishing Mach Machine

Technical Specification :

Features:

Robust construction.

Easy installation.

Compact size.

Main Parameter:

Diameter of the polishing and grinding disc: 230mm

Diameter of the abrasive paper: 230mm

Motor of grinding head: DC brushless deceleration motor, two-phase 220V 400W

Or four-speed 250r/min, 500r/min, 750r/min, 1000r/min

Rotational speed: 100-1000r/min, stepless

Motor: DC brushless motor,two-phase 220V 400W

Cylinder pressure: adjustable (Suggest 0.2~0.3mpa)

Rotational speed of grinding head: 20~120r/min, stepless

Net weight: 50Kg

External dimension: 420-623-645mm (include PDZ automatic grind head)

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg,Ambala Cantt,Haryana,India. **Phone:** +91-9896600003