

**Product Name :**  
Nauga Spectro Double Polisher Machine

**Product Code :**  
NLAB-ENGINEERINGLB84008



**Description :**

Nauga Spectro Double Polisher Machine

**Technical Specification :**

This Machine is very useful for preparation outer body made of thick M. steel with powder coated rust proof paint.

Made of steel with air gripping arrangement to alundum disc with the locking system to keep the alundum disc in position.

Main motor: 2 H.P, 2800 R.P.M.: 440 / 460 volt 3 phase AC supply.

Machine to suit disc housing and to cover the disc plate by 180 deg. for safety.

L & T make push button type for the main and gripping motor.

H.P, 2800 R.P.M.: 440 / 460 volt 3 phase AC supply.

**Features:**

Rugged construction.

Easy to use.

Require less maintenance.

## Naugralabequipments

**Website:** [www.naugralabequipments.com](http://www.naugralabequipments.com), **Email:** [sales@naugralabequipments.com](mailto:sales@naugralabequipments.com)

**Address:** 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003