

Product Name :
OPTO Coupler Characteristics Analog Meters

Product Code :
NLAB-ELECTRICALAB210034



Description :

OPTO Coupler Characteristics Analog Meters

Technical Specification :

SCOPE OF LEARNING:

Study of V-I Characteristics of OPTO COUPLER OR MCT

TECHNICAL SPECIFICATIONS:

Analog Meters:

Ammeter 10mA DC.

Ammeter 10mA DC.

Voltmeter 10V DC.

Power Supplies:

DC Supply IC Regulated 0-10V DC, 150mA.

DC Supply IC Regulated 0-10V DC, 150mA.

Operated on Mains power 230V, 50Hz +10%

Components are mounted on the panels are:

OPTO COUPLER

Voltage Control through Potentiometer.

SALIENT FEATURES:

Front panel built with high class insulated Printed Circuit Board sheet with well printed circuits and symbols.

Fuse for Short Circuit protection

Instruction manual.

Connections are brought out through 4mm Colored Sockets.

Patch Cords 4mm.

The trainer is housed in ABS Plastic cabinet.

Size of the trainer set 12"x8"

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003