

Product Name :
Pedestal Grinder With Coolant & Fittings

Product Code :
NLAB-MACHINELABWK22014



Description :

Pedestal Grinder With Coolant & Fittings

Technical Specification :

Pedestal Grinder With Coolant & Fittings .

WHEEL FLANGES - Wheel flanges are of balanced design, the inner pair keyed to the spindle for positive drive for 18" to 40 " grinders.

TOOL RESTS - These are adjustable both in horizontal and vertical positions for allowing maximum wear and tear of the wheels.

DRIVE - Through V-belts to the spindle by an Electric Motor. Two speeds are provided to maintain peripheral speeds when the wheels wear out.

ELECTRICALS - 400/440 volts 3 phase 50 cycles ISI Mark Electric Motor with LT/LK/BETEX Push button starter direct on line with overload, undervoltage.

SPECIAL ACCESSORIES AT EXTRA COST: Coolant equipment, Twist drill Grinding Attachment, Dust Exhaust Equipment, Machine Light, Water Pot and Foundation Nuts & Bolts.

500
750
500
0000 Centre Distance

SPINDLE
000 Centre height
000M.

ELECTRIC MOTOR
00P. 3 Phase

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg,Ambala Cantt,Haryana,India. **Phone:** +91-9896600003