

Product Name :
Plastic 3D Printer

Product Code :
AR995



Description :

Plastic 3D Printer

Technical Specification :

Plastic 3D Printer

System Properties

Interface Ethernet connection

USB (direct printing)

Software 3D Sprint

Power input Printer With adaptor

24V DC, 3.75A

100-240V AC, 2A, 50/60 Hz

Printing Specifications

Build size 125 x 70 x 120 mm (4.92 x 2.76 x 4.72 in)*

Pixel Pitch 65 microns (0.0025 in) (390.8 effective DPI)

Layer Thickness 30-100 microns (0.0012 to 0.004 in) (material dependent)

Wavelength 405 nm

Operating Environment

Temperature 18-28 °C (64-82 °F)

Humidity (RH) 30-70 %

Accessories

LC-3DPrint Box

Load Capacity (Width x Depth x Height) 260 x 260 x 195 mm

Dimensions (Width x Length x Height) 41 x 44 x 38 cm

Full light spectrum 300-550 nm
Weight 22 kg
Electrical 230 V, 50 Hz, 2.6/1.3 A.

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003