

**Product Name :**  
Precision Bending Brake

**Product Code :**  
NLAB-MACHINELABWK24007



**Description :**

Precision Bending Brake

**Technical Specification :**

Precision Bending Brake .

A multitude of forming and duplicating operations can be performed with leaf type Precision bending brakes in experimental and production quantities. Particularly for the "Small" jobs such as making of closed boxes and chasis for appartus Radio cabinet parts etc. Precision bending brakes are extremely handy as to this last, the versatile possibilities of the finger combinations are self evident.

**Maximum forming width mm**

**Material capacity - Mild Steel swg.**

~~1250~~mm  
bending angle

~~25~~mm  
clearance  
through top  
opening mm

Undercut box  
fingers (for  
forming

~~15~~mm  
boxes with  
lipped or  
flanged edges-  
mm)

~~20~~mm  
effective  
finger depth-  
mm

~~10~~mm  
Minimum  
reverse bends-  
mm

Back gauge  
adjustment

~~100~~mm  
(can be  
increased)  
mm

~~100~~mm  
prox.  
weight Kgs.

## Naugralabequipments

**Website:** www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

**Address:** 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003