


**Product Name :**  
Precision Bending Brake

**Product Code :**  
NLAB-MACHINELABWK24007



**Description :**

Precision Bending Brake

**Technical Specification :**

Precision Bending Brake .

A multitude of forming and duplicating operations can be performed with leaf type Precision bending brakes in experimental and production quantities. Particularly for the "Small" jobs such as making of closed boxes and chasis for appartus Radio cabinet parts etc. Precision bending brakes are extremely handy as to this last, the versatile possibilities of the finger combinations are self evident.

**Maximum  
forming width  
mm**

**Material  
capacity - Mild  
Steel swg.**

1250mm  
bending angle  
254mm  
clearance  
through top  
opening mm  
Undercut box  
fingers (for  
forming  
boxes with  
lipped or  
flanged edges-  
mm)  
200mm  
effective  
finger depth-  
mm  
Minimum  
reverse bends-  
mm  
Back gauge  
adjustment  
100mm  
(can be  
increased)  
mm  
1000  
prox.  
weight Kgs.

## Naugralabequipments

**Website:** www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

**Address:** 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003