

**Product Name :**  
Shearing Machine

**Product Code :**  
MU854



**Description :**

**Shearing Machine**

**Technical Specification :**

Shearing Machine 1000mm, capable to cut up to 2mm  
Foot operated Shearing machine is designed and developed for accurate burr-free cutting of thin or thick sheet in strength, it helps to get more production in time, two best quality of spring provided for quick return of ram (Upper Beam), fitted with side, back, front gauges and table extension.  
This machine is suitable to cut M.S., S.S., Copper, Brass, Aluminium, P.V.C., P.C.B., CRC, CRGO, CRNGO, G.R Sheets and etc. Also applicable to M.S., S.S cutting, Block maker, Furniture, Fabricators, Tube light patty, Colander rim, Electrical fitting, Electronics, Tin container, RP Caps, Electrical and transformers stamping industries.

## Naugralabequipments

**Website:** www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

**Address:** 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003