

**Product Name :**  
Soldering and De-Soldering Station

**Product Code :**  
NLAB-ELECTRONICSAB370006



**Description :**

Soldering and De-Soldering Station

**Technical Specification :**

Input Voltage : 190 V to 270C

Output Voltage : 24VAC

Soldering Wattage : 60 Watts

De-Soldering Wattage : 70 Watts

Temp Range : 180 – 480°C

Temp Accuracy :  $\pm 1^\circ\text{C}$

Tip to ground potential : Under 2MV

Tip to ground Leakage : Under 2

Vacuum : 600mm/Hg

Accessories :

Control Unit 1 No.

Soldering Iron 1 No.

De-Soldering Iron 1 No.

Combined Soldering & De-Soldering Stand 1 No.

Power Cord- 1 No.

## Naugralabequipments

**Website:** www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

**Address:** 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003