

Product Name :
The Complete Rework Station

Product Code :
NLAB-ELECTRONICSAB370008



Description :

The Complete Rework Station

Technical Specification :

Clear LCD Display

Nine Simultaneously Operations, all nine Ops Independent

Completely Indigenously developed

The Mini Lab Features in a tabletop Unit

System Includes:-

Soldering Station : 24V / 60W

De-Soldering Stations : 24V / 70W

Thermal wire Stripper

DC Power Supplies : 1.5V to 18V DC

SMD Hot Air (with Built in Vacuum Pick Up)

SMT Hot Tweezer (2 x 25W)

Electric Screw driver

Machine Center (Micro Drilling, Milling,)

Auto Range Multimeter

De-Soldering Irons:-

Input Voltage : 190 V to 27V

Output Voltage : 24VAC

Soldering element : 60 W

De-Soldering element : 70W

Temp range : 180-480 Deg.C

Temp Accuracy : ± 1 deg.c

Tip to ground Potential : Under 2MV

Tip to Ground leakage : Under 2 E

Vacuum : 600mm/Hg.

High Quality 24 V DC Pump with 4000 RPM

SMD Hot Air:-

Input Voltage : 220VAC

Power Consumption : 300 W

Air Pump : Diaphragm Type

Capacity : 24 L / min

Hot Air Temperature : 200 to 550 Deg. C

SMTTweezer : 2 x 25 W

Thermal Wire Stripper : 1.5V / 1Amps

Quick heat Up : With in 2 Seconds

Stepless increase of Temperature

(Soft PVC to tough PTFE / Teflon)

Electric screw driver

Machine Centre

DC power Supplies : 1.5V – 15V DC / 1Amps

Auto Range Multimeter

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003