

Product Name :
TVET Clamp On Meter

Product Code :
NLAB-EDUCATIONTVET32001



Description :

TVET Clamp On Meter

Technical Specification :

Type of meter AC/DC digital clamp meter

Max. diameter of measured cable 45mm

Kind of display used LCD (6666), with a backlit

DC current measuring range 66A/1kA

AC current measuring range 66A/1kA

DC current measuring accuracy $\pm(2\% + 8 \text{ digits})$

AC current measuring accuracy $\pm(2\% + 8 \text{ digits})$

DC voltage measuring range 1mV...6.6V/66V/600V

DC voltage measuring accuracy $\pm(0.8\% + 1 \text{ digit})$

AC voltage measuring range 1mV...6.6V/66V/600V

AC voltage measuring accuracy $\pm(1.2\% + 5 \text{ digits})$

True effective value measurement True RMS

Resistance measuring range 100m Ω ...660 Ω /6.6k Ω /66k Ω /660k Ω /6.6M Ω /66M Ω

Resistance measuring accuracy $\pm(1\% + 2 \text{ digits})$

Frequency measuring range 100mHz...660Hz/6.6kHz/66kHz/660kHz/6.6MHz/66MHz

Duty cycle factor 0.1...99.9%

Continuity test acoustic signal for $R < 10\Omega$

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003