

Product Name :
TVET Well Logging

Product Code :
NLAB-EDUCATIONTVET40004



Description :

TVET Well Logging

Technical Specification :

The use of the environment?Power supply: 220V, 50 Hz?Using the environment temperature: -20? ~ 45??Using the environment humidity: 90% or less (45?)

The depth measurement system?Depth measurement range: 0 ~ 9999.99 m?Depth resolution: 0.28 mm?Speed ??measurement range: 0 ~ 9999m/h?Deep optical pulse

signal: 3600 pulses per meter

Signal transmission system? Bottom hole output signal: bipolar coding?Communication with the computer: RS232 or USB?The underground signal detection level:

plus or minus 0.5V ~ plus or minus 12V

Figure out the depth of the graph; 1:10; 1:50. 1:100. 1:0; 1, 50, 0, etc.

The drawing accuracy?8 points per millimeter (curve)?64 pixels per square millimeter (image method).

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003